





UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES. TOLERANCE:
 X = ± .125
 XX = ± .0625
 XXX = ± .03125
 FINISH ✓
 ANGLES ± .5° HOLE DIA. ± .005
 CONFORMS TO ASME Y14.5M-1994.

DATE: [REDACTED]
 DRAWN BY: [REDACTED]
 DO NOT SCALE PRINT
 DATE: [REDACTED]
 THIRD ANGLE PROJECTION


15' BASE SHEET 1 OF 1
 RTAC
 140T STD/ HCH
 155T STD
 170T STD



DETAIL A



DETAIL B



.25 HEIGHT OF LIFTING PLATES FROM FLOOR.

