

DRAWING
REVISION
C
VERSION
0

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES. TOLERANCE:



.X = ± 0.1
 .XX = ± 0.06
 .XXX = ± 0.003
 ANGLES = ± 2.0 °
 HOLE DIA = ± 0.005
 CONFORMS TO ASME Y14.5M-1994.

FINISH ✓
 + 0.005
 - 0.005

TRANE
 THIS DRAWING IS PROPRIETARY AND SHALL NOT BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS WITHOUT THE WRITTEN CONSENT OF TRANE
 DRAWN BY: M. MAYES
 DATE: 30-AUG-2018
 THIRD ANGLE PROJECTION
 DO NOT SCALE PRINT

X15010039
 VALVE
 AIR VENT; AUTOMATIC
 REV C
 SHEET 1 OF 1

SPECIFICATIONS:
 BODY: CUZM40PB2
 CHECK VALVE: STAINLESS STEEL
 SEAL: EPDM
 HYGROSCOPIC DISC: SPECIAL CELLULOSE
 HANDWHEEL: ABS
 MAXIMUM TEMP: 230°F
 MAXIMUM PRESSURE: 125 PSI
 FLUID: WATER



D

C

B

A

4

3

2

1