



General VRF Product Bulletin

Product Option Codes

February 19, 2018

From: Trane Ductless Product Support

Introduction

The purpose of this Product Bulletin is to discuss the installation option codes for Trane ProSpace™ VRF, and Mini-Split products. This Product Bulletin is for informational purposes only and should not be distributed.

Affected Units

The information in this Product Bulletin is applicable to the Trane ProSpace™ VRF, and Mini-Split models as noted below. This bulletin is specific to units which have been, or will be manufactured for sale by Trane North America between 2015 through 2018. This Product Bulletin does not apply to any other products, or product accessories not specified herein.

Affected VRF Model Indoor Unit (IDU) prefixes include; *4TVA; 4TVB; 4TVC; 4TVD; 4TVE; 4TVF; 4TVL; 4TVM; 4TVS; 4TVW; 4TVX.*

Affected VRF Mini-Split Indoor Unit (IDU) prefixes include: *4MUC; 4MUD; 4MUS; 4MUW*

Discussion

It is occasionally desirable to change the performance characteristics of an IDU after it has shipped. Reasons for making these modifications include:

- Modifications to the project design
- Changes to project building envelope
- Stock and availability requirements
- Other unforeseen complications

Trane ProSpace™ VRF, and Mini-Split Indoor Units (IDU) often use similar chassis for different capacity sizes. While the internal components of these IDUs may be similar, the operation of the components does vary based on proprietary controls protocols for each model. It is therefore sometimes possible to only change the protocol, and achieve the same performance as a larger or smaller model. When authorized, and executed in cooperation with Trane, the installation option changes shall not affect applicable product warranties.

When modifying VRF IDUs, all changes must be verified using the VRF Select Selection tool. If the installation option code changes the VRF Select solution in anyway, the job site requirements must be modified to comply with the revised solution. This includes but is not limited to piping, controls wiring, controls interfaces, and various other accessories. Failure to comply with this requirement will void warranty, as well as product and technical support.

When modifying Mini-Split IDUs, all changes must be verified using the published literature for the new model number. This includes but is not limited to piping, controls wiring, controls interfaces, and various other accessories. Failure to comply with this requirement will void warranty, as well as product and technical support.

Determination

When factory approved, it is sometimes possible to field modify specific Trane ProSpace™ VRF, and or Mini-Split IDU models to increase or decrease performance using only the product option code. The product option codes are listed below.

When authorized and executed in cooperation with Trane, the changes will have no impact on warranty requirements. Where required, new nameplates may be obtained that reflect the updated performance and model number.

The list below details units that may interchange product option codes. Only units within the same sub-family are compatible for product option code modification. For example, a sub-family is the 4TVC; 4-Way Cassette (small). These models are not convertible to a 4TVC; 4-Way Cassette (large).

If a model is not specifically listed as a compatible model number, it has a unique EEV, coil, and blower combination. Models with unique combinations, are not approved for product code substitution.

Units that may Substitute Product Option Codes

VRF Product Families:

Compatible Model Numbers:

4TVA; HSP Duct	4TVA0076D100N*; 0096
4TVB; 4-Way Mini Cassette	4TVB0005B100N*; 0007; 009; 0012; 0018; 0020
4TVC; 4-Way Cassette (small)	4TVC0009B100N*; 0012; 0018; 0024
4TVC; 4-Way Cassette (large)	4TVC0030B100N*; 0036; 0048
4TVD; MSP Duct 2 nd Gen (small)	4TVD0007C100N*; 0009; 0012; 0015
4TVD; MSP Duct 2 nd Gen (medium)	4TVD0024C100N*; 0027; 0030
4TVD; MSP Duct 2 nd Gen (large)	4TVD0036C100N*; 0048
4TVD; MSP Duct 3 rd Gen (small)	4TVD0007D100N*; 0009; 0012; 0015; 018
4TVD; MSP Duct 3 rd Gen (medium)	4TVD0024D100N*; 0027; 0030

VRV Product Families (cont.):

4TVD; MSP Duct 3rd Gen (large)
4TVE; 1-Way Cassette
4TVF; Floor Cabinet-Recessed (small)
4TVF; Floor Cabinet-Recessed (large)
4TVL; Slim Duct (small)
4TVL; Slim Duct (medium)
4TVL; Slim Duct (large)
4TVM; Convertible AHU
4TVS; Circular Cassette (small)
4TVS; Circular Cassette (large)
4TVW; High wall 2nd Gen (small)
4TVW; High wall 2nd Gen (large)
4TVW; High wall 3rd Gen (small)
4TVW; High wall 3rd Gen (large)
4TVX; Ceiling-Floor

**wildcard for 14th digit. May be A, B, C, or D*

Compatible Model Numbers:

4TVD0036D100N*; 0048
4TVE0007B100N*; 0009; 0012
4TVF0006B10*N*; 0009; 0012
4TVF0018B10*N*; 0024
4TVL0007B100N*; 0009; 0012
4TVL0018B100N*; 0024
4TVL0030B100N*; 0036
4TVM0009C100NB; 0012;
4TVS0009B100N*; 0012; 0018; 0024
4TVS0030B100N*; 0036; 0048
4TVW0007B100N*; 0009; 0012
4TVW0018B100N*; 0020; 0024
4TVW0005D100N*; 0007
4TVW0018D100N*; 0024; 0027
4TVX0018B100N*; 0024

Mini-Split Product Families:

4MUC; 4-Way Cassette (small)
4MUC; 4-Way Cassette (large)
4MUD; Ducted (small)
4MUD; Ducted (large)
4MUS; Circular Cassette (small)
4MUS; Circular Cassette (large)
4MUW; High Wall

**wildcard for 14th digit. May be A, B, C, or D*

Compatible Model Numbers:

4MUC4518A10N0*; 4524
4MUC4530A10N0*; 4536; 4542; 4548
4MUD4518A10N0*; 4524
4MUD4530A10N0*; 4536; 4542; 4548
4MUS4518A10N0*; 4524
4MUS4530A10N0*; 4536; 4542; 4548
4MUW4530A10N0*; 4536

VRF Product Option Codes

TYPE		MODEL NUMBER	Static Pressure	Option
1 Way Cassette		4TVE0007B100N*	-	017044-1180C8-201616-330010
		4TVE0009B100N*	-	017044-1180F8-201C1C-330010
		4TVE0012B100N*	-	017044-11545D-202323-330010
4 Way Cassette	Small	4TVC0009B100N*	-	014047-195064-201A1A-330000
		4TVC0012B100N*	-	014047-195097-203434-330000
		4TVC0018B100N*	-	014047-1950C7-204848-330000
	Large	4TVC0024B100N*	-	014047-195409-205A5A-330020
		4TVC0036B100N*	-	014047-19541B-206E6E-330020
		4TVC0048B100N*	-	014047-19544F-209191-330020
Mini 4 Way Cassette		4TVB0005B100N*	-	01504F-1970B8-200F0F-330000
		4TVB0007B100N*	-	01504F-1970E8-201616-330000
		4TVB0009B100N*	-	01504F-19540A-201C1C-330000
		4TVB0012B100N*	-	01504F-19342C-202323-330000
		4TVB0018B100N*	-	01504F-19547F-203434-330000
		4TVB0020B100N*	-	01504F-195591-203C3C-330000
AHU Kit		4EEVAKA40K1025	-	01A054-105000-204646-331100
		4EEVAKA40K1050	-	01A054-105000-208C8C-331100
		4EEVAKA64K1075	-	01A054-105000-20D2D2-331100
		4EEVAKA64K1100	-	01A054-105000-231C1C-330100
Ceiling		4TVX0018B100N*	-	013054-105000-203434-330010
		4TVX0024B100N*	-	013054-105000-204848-330010
Circular Cassette	Small	4TVS0009B100N*	-	01004F-1950E9-201A1A-330000
		4TVS0012B100N*	-	01004F-1950E9-202121-330000
		4TVS0018B100N*	-	01004F-1950E9-203434-330000
	Large	4TVS0024B100N*	-	01004F-1950E9-204848-330000
		4TVS0030B100N*	-	01004F-19542D-205A5A-330000
		4TVS0036B100N*	-	01004F-19545F-206E6E-330000
		4TVS0048B100N*	-	01004F-195581-209191-330000
Convertible AHU		4TVM0009C100N*	-	01A054-105000-202323-331100
		4TVM0012C100N*	-	01A054-105000-202323-331100
		4TVM0018C100N*	-	01A054-105000-203535-331100
		4TVM0024B100N*	-	01A054-105000-204646-331100
		4TVM0030B100N*	-	01A054-105000-204646-331100
		4TVM0036B100N*	-	01A054-105000-208C8C-331100
		4TVM0042B100N*	-	01A054-105000-208C8C-331100
		4TVM0048B100N*	-	01A054-105000-208C8C-331100
		4TVM0060B100N*	-	01A054-105000-208C8C-331100
DOAU	4TVN0072A100N*	0.2"	01B064-193020-231515-333000	
		0.4"	01B064-193051-231515-333000	
		0.6"	01B064-193097-231515-333000	
		0.8"	01B064-1930EC-231515-333000	
		1.0"	01B064-19343E-231515-333000	
		1.1"	01B064-19348E-231515-333000	
		4TVN0096A100N*	0.2"	01B064-193030-231C1C-333000
	0.4"	01B064-193061-231C1C-333000		
	0.6"	01B064-1930A8-231C1C-333000		
	0.8"	01B064-19340E-231C1C-333000		
	1.0"	01B064-19345E-231C1C-333000		
	1.1"	01B064-1934AE-231C1C-333000		

VRF Product Option Codes (continued)

TYPE		MODEL NUMBER	Static Pressure	Option
Floor Standing	Recessed/ Exposed	4TVF0006B10*N*	-	01A054-105000-201212-330010
		4TVF0009B10*N*	-	01A054-105000-201C1C-330010
		4TVF0012B10*N*	-	01A054-105000-202323-330010
		4TVF0018B10*N*	-	01A054-105000-203434-330010
		4TVF0024B10*N*	-	01A054-105000-204848-330010
High Wall (with EEV) 2nd Gen	Small	4TVW0007B100N*	-	010044-1170FA-201616-330001
		4TVW0009B100N*	-	010044-1170FA-201C1C-330000
		4TVW0012B100N*	-	010044-11744D-202323-330000
	Large	4TVW0018B100N*	-	010044-11645E-203434-330020
		4TVW0020B100N*	-	010044-11646F-203C3C-330020
High Wall (with EEV) 3rd Gen	Small	4TVW0005D100N*	-	012044-1990D9-200F0F-310000
		4TVW0007D100N*	-	012044-19942A-201616-310000
		4TVW0009D100N*	-	012044-19945C-201C1C-310000
		4TVW0012D100N*	-	012044-19845E-202424-310010
		4TVW0015D100N*	-	012044-1955A2-202D2D-310010
	Large	4TVW0018D100N*	-	012044-19942C-203838-310020
		4TVW0024D100N*	-	012044-19847F-204747-310020
		4TVW0027D100N*	-	012044-1955A3-205252-310020
		4TVW0030C100N*	-	013044-19746E-205D5D-310020
HSP	BIG DUCT	4TVA0076B100N*	0.2"	011054-195097-20DCDC-331110
			0.4"	011054-1950C7-20DCDC-331110
			0.6"	011054-1950E8-20DCDC-331110
			0.8"	011054-19544D-20DCDC-331110
			1.0"	011054-19549F-20DCDC-331110
		4TVA0096B100N*	0.2"	011054-195407-231C1C-331110
			0.4"	011054-195429-231C1C-331110
			0.6"	010054-19545B-231C1C-331110
			0.8"	011054-19549E-231C1C-331110
			1.0"	011054-1955D1-231C1C-331110
MSP Duct (2nd Gen)	Small	4TVD0007C100N*	0.04"	010054-1B5095-201616-331110
			0.12"	010054-1B50F8-201616-331110
			0.20"	010054-1B544B-201616-331110
			0.3"	010054-1B549E-201616-331110
			0.4"	010054-1B55D1-201616-331110
			0.5"	010054-1B5913-201616-331110
			0.6"	010054-1B5956-201616-331110
			4TVD0009C100N*	0.04"
		0.12"		010054-1B50FA-201C1C-331110
		0.20"		010054-1B544D-201C1C-331110
		0.3"		010054-1B5591-201C1C-331110
		0.4"		010054-1B55E4-201C1C-331110
		0.5"		010054-1B5917-201C1C-331110
		0.6"		010054-1B595A-201C1C-331110
		4TVD0012C100N*		0.04"
			0.12"	010054-1B5409-202323-331110
			0.20"	010054-1B545C-202323-331110
			0.3"	010054-1B54AF-202323-331110
			0.4"	010054-1B55F2-202323-331110
			0.5"	010054-1B5934-202323-331110
			0.6"	010054-1B5967-202323-331110

VRF Product Option Codes (continued)

TYPE		MODEL NUMBER	Static Pressure	Option	
MSP Duct (2nd Gen)	Small	4TVD0015C100N*	0.04"	010054-1B50F9-202C2C-331110	
			0.12"	010054-1B544D-202C2C-331110	
			0.20"	010054-1B5580-202C2C-331110	
			0.3"	010054-1B55D3-202C2C-331110	
			0.4"	010054-1B5915-202C2C-331110	
			0.5"	010054-1B5968-202C2C-331110	
		4TVD0018C100N*	0.6"	010054-1B59AB-202C2C-331110	
			0.04"	010054-1B542C-203535-331110	
			0.12"	010054-1B5570-203535-331110	
			0.20"	010054-1B55B4-203535-331110	
			0.3"	010054-1B5907-203535-331110	
			0.4"	010054-1B594A-203535-331110	
		Medium	4TVD0024C100N*	0.5"	010054-1B599D-203535-331110
				0.6"	010054-1B5AD0-203535-331110
	4TVD0027C100N*			0.2"	010054-1355A6-204646-331110
				0.3"	010054-1355F9-204646-331110
				0.4"	010054-13594E-204646-331110
				0.5"	010054-135A70-204646-331110
			0.6"	010054-135AA3-204646-331110	
			0.7"	010054-135AE6-204646-331110	
	4TVD0030C100N*		0.8"	010054-135E18-204646-331110	
			0.2"	010054-1355C7-204F4F-331110	
			0.3"	010054-13591C-204F4F-331110	
			0.4"	010054-13595F-204F4F-331110	
			0.5"	010054-135A93-204F4F-331110	
			0.6"	010054-135AC5-204F4F-331110	
	Large		4TVD0036C100N*	0.7"	010054-135E08-204F4F-331110
				0.8"	010054-135E3A-204F4F-331110
				0.2"	010054-1355D8-205858-331110
				0.3"	010054-13593A-205858-331110
				0.4"	010054-13598E-205858-331110
				0.5"	010054-135AB1-205858-331110
			4TVD0048C100N*	0.6"	010054-135AF4-205858-331110
				0.7"	010054-135E37-205858-331110
				0.8"	010054-135E59-205858-331110
				4TVD0054C100N*	0.2"
		0.3"			010054-135A70-206969-331110
		0.4"			010054-135AB4-206969-331110
	0.5"	010054-135AF7-206969-331110			
	0.6"	010054-135E39-206969-331110			
	0.7"	010054-135E6C-206969-331110			
	4TVD0054C100N*	0.8"	010054-135EAF-206969-331110		
		0.2"	010054-135A60-208D8D-331110		
		0.3"	010054-135AC5-208D8D-331110		
		0.4"	010054-135E18-208D8D-331110		
		0.5"	010054-135E5B-208D8D-331110		
		0.6"	010054-135E9F-208D8D-331110		
	4TVD0054C100N*	0.7"	010054-135FB2-208D8D-331110		
		0.8"	010054-135FC5-208D8D-331110		
		0.2"	010054-135E07-209E9E-331110		
	4TVD0054C100N*	0.3"	010054-135E4A-209E9E-331110		
		0.4"	010054-135E8D-209E9E-331110		

VRF Product Option Codes (continued)

TYPE		MODEL NUMBER	Static Pressure	Option
MSP Duct (2nd Gen)	Large	4TVD0054C100N*	0.4"	010054-135E8D-209E9E-331110
			0.5"	010054-135FB1-209E9E-331110
			0.6"	010054-135FC4-209E9E-331110
MSP Duct (3rd Gen)	Small	4TVD0007D100N*	0.04"	010054-1E5060-201616-331100
			0.12"	010054-1E50D4-201616-331100
			0.20"	010054-1E5437-201616-331100
			0.3"	010054-1E54DA-201616-331100
			0.4"	010054-1E581E-201616-331100
			0.5"	010054-1E5972-201616-331100
			0.6"	010054-1E59C5-201616-331100
		4TVD0009D100N*	0.04"	010054-1E5060- 201C1C-331101
			0.12"	010054-1E50D4- 201C1C-331101
			0.20"	010054-1E5437- 201C1C-331101
			0.3"	010054-1E54AA- 201C1C-331101
			0.4"	010054-1E581E- 201C1C-331101
			0.5"	010054-1E5972- 201C1C-331101
			0.6"	010054-1E59C5- 201C1C-331101
		4TVD0012D100N*	0.04"	010054-1E5072- 202323-331102
			0.12"	010054-1E50D6- 202323-331102
			0.20"	010054-1E5449- 202323-331102
			0.3"	010054-1E54BD- 202323-331102
			0.4"	010054-1E5911- 202323-331102
			0.5"	010054-1E5976- 202323-331102
			0.6"	010054-1E59CA- 202323-331102
		4TVD0018D100N*	0.04"	010054-1E5438- 203535-331104
			0.12"	010054-1E549B- 203535-331104
			0.20"	010054-1E54FF- 203535-331104
	0.3"		010054-1E5944- 203535-331104	
	0.4"		010054-1E59A9- 203535-331104	
	0.5"		010054-1E59EC- 203535-331104	
	0.6"		010054-1E5E30- 203535-331104	
	Medium	4TVD0024C100N*	0.2"	010054-1E54BB- 204646-331115
			0.3"	010054-1E581F- 204646-331115
			0.4"	010054-1E5973- 204646-331115
			0.5"	010054-1E59C6- 204646-331115
			0.6"	010054-1E5D1A- 204646-331115
			0.7"	010054-1E5D6D- 204646-331115
			0.8"	010054-1E5EA0- 204646-331115
			4TVD0027D100N*	0.2"
		0.3"		010054-1E5924- 204F4F-331115
		0.4"		010054-1E5989- 204F4F-331115
		0.5"		010054-1E59DC- 204F4F-331115
		0.6"		010054-1E5E20- 204F4F-331115
		0.7"		010054-1E5E63- 204F4F-331115
		0.8"		010054-1E5EB7- 204F4F-331115
		4TVD0030C100N*		0.2"
			0.3"	010054-1E5938- 205858-331116
			0.4"	010054-1E598C- 205858-331116
			0.5"	010054-1E5AE1- 205858-331116
			0.6"	010054-1E5E35- 205858-331116
			0.7"	010054-1E5E78- 205858-331116
0.8"			010054-1E5ECC- 205858-331116	

VRF Product Option Codes (continued)

TYPE		MODEL NUMBER	Static Pressure	Option		
MSP Duct (3rd Gen)	Large	4TVD0036D100N*	0.2"	010054-1E542A- 206969-331124		
			0.3"	010054-1E546C- 206969-331124		
			0.4"	010054-1E55B0- 206969-331124		
			0.5"	010054-1E55F3- 206969-331124		
			0.6"	010054-1E5936- 206969-331124		
			0.7"	010054-1E597A- 206969-331124		
		4TVD0048D100N*	0.2"	010054-1E548D- 208D8D-33112A		
			0.3"	010054-1E55C0- 208D8D-33112A		
			0.4"	010054-1E55F2- 208D8D-33112A		
			0.5"	010054-1E5935- 208D8D-33112A		
			0.6"	010054-1E5989- 208D8D-33112A		
			0.7"	010054-1E59CC- 208D8D-33112A		
		Slim Duct	Small	4TVL0007B100N*	0"	010054-1254AE-201616-331110
					0.04"	010054-1255D1-201616-331110
0.08"	010054-1255D1-201616-331110					
0.16"	010054-125904-201616-331110					
4TVL0009B100N*	0"			010054-121913-201C1C-331110		
	0.04"			010054-121946-201C1C-331110		
	0.08"			010054-121946-201C1C-331110		
	0.16"			010054-121979-201C1C-331110		
4TVL0012B100N*	0"			010054-121946-202323-331110		
	0.04"			010054-121979-202323-331110		
	0.08"			010054-121979-202323-331110		
	0.16"			010054-1219AC-202323-331110		
Medium	4TVL0018B100N*		0"	010054-1259BA-203434-331110		
			0.04"	010054-1259ED-203434-331110		
			0.08"	010054-1259ED-203434-331110		
			0.16"	010054-125E10-203434-331110		
	4TVL0024B100N*		0"	010054-125D2D-204848-331110		
			0.04"	010054-125E50-204848-331110		
			0.08"	010054-125E50-204848-331110		
			0.16"	010054-125E83-204848-331110		
Large	4TVL0030B100N*		0"	010054-1B5915-205A5A-331110		
			0.04"	010054-1B5948-205A5A-331110		
			0.12"	010054-1B599F-205A5A-331110		
			0.24"	010054-1B5AE4-205A5A-331110		
	4TVL0036B100N*		0"	010054-1B5956-206E6E-331110		
			0.04"	010054-1B5989-206E6E-331110		
			0.12"	010054-1B5AD0-206E6E-331110		
			0.24"	010054-1B5E25-206E6E-331110		
	4TVL0048B100N*	0"	010054-1B59B9-209191-331110			
		0.04"	010054-1B59EC-209191-331110			
		0.12"	010054-1B5E33-209191-331110			
		0.24"	010054-1B5E88-209191-331110			

Mini-Split Product Option Codes

TYPE		MODEL NUMBER	Static Pressure	Option
4 Way Cassette	Small	4MUC4518A10N0*	-	01406F-1950D8-27343B-370005
		4MUC4524A10N0*	-	01406F-1950D8-274750-370005
		4MUC4530A10N0*	-	01406F-1950E8-275A64-370045
	Large	4MUC4536A10N0*	-	01406F-195439-276470-370045
		4MUC4542A10N0*	-	01406F-19544A-277D8C-370045
		4MUC4548A10N0*	-	01406F-19545B-278CA0-370045
Circular Cassette	Small	4MUS4518A10N0*	-	0100EF-1950D8-27343B-370005
		4MUS4524A10N0*	-	0100EF-1950D8-274750-370005
		4MUS4530A10N0*	-	0100EF-19541A-275A64-370045
	Large	4MUS4536A10N0*	-	0100EF-19548C-276470-370045
		4MUS4542A10N0*	-	0100EF-19549D-277D8C-370045
		4MUS4548A10N0*	-	0100EF-1954AF-278CA0-380045
Convertible AHU		4MUM4518A10N0*	-	01E06C-105020-27343B-370005
		4MUM4524A10N0*	-	01E06C-105020-274750-370005
		4MUM4530A10N0*	-	01E06C-105020-275A64-370005
		4MUM4536A10N0*	-	01E06C-105020-276470-370005
		4MUM4542A10N0*	-	01E06C-105020-277D8C-370005
		4MUM4548A10N0*	-	01E06C-105020-278CA0-370005
High Wall (with EEV)		4MUW4512A10N0*	-	0100FC-19548C-272328-371708
		4MUW4518A10N0*	-	0100FC-19548E-27343E-3C170D
		4MUW4524A10N0*	-	0100FC-19547F-274750-37170D
		4MUW4530A10N0*	-	0110FC-193573-275A64-37770D
		4MUW4536A10N0*	-	0110FC-194594-276470-39670D
MSP Duct (2nd Gen)	Small	4MUD4518A10N0*	0.12"	01C0EC-1C8424-27343B-370005
			0.2"	01C0EC-1C5468-27343B-370005
			0.3"	01C0EC-1C54CE-27343B-370005
			0.4"	01C0EC-1C5924-27343B-370005
			0.5"	01C0EC-1C596A-27343B-370005
			0.6"	01C0EC-1C59CE-27343B-370005
		4MUD4524A10N0*	0.12"	01C0EC-1C747C-274750-370005
			0.2"	01C0EC-1C54AF-274750-370005
			0.3"	01C0EC-1C55E6-274750-370005
			0.4"	01C0EC-1C595A-274750-370005
			0.5"	01C0EC-1C5AB0-274750-370005
			0.6"	01C0EC-1C5AE3-274750-370005
	Large	4MUD4530A10N0*	0.16"	0100EC-1A55D4-275A64-370005
			0.28"	0100EC-1A5927-275A64-370005
			0.4"	0100EC-1A594A-275A64-370005
			0.5"	0100EC-1A598C-275A64-370005
			0.6"	0100EC-1A59BE-275A64-370005
			0.7"	0100EC-1A5AE0-275A64-370005
		4MUD4536A10N0*	0.8"	0100EC-1A5E02-275A64-370005
			0.16"	0100EC-1A5902-276470-370005
			0.28"	0100EC-1A595A-276470-370005
			0.4"	0100EC-1A598C-276470-370005
			0.5"	0100EC-1A59BE-276470-370005
			0.6"	0100EC-1A5AE0-276470-370005

Mini-Split Product Option Codes (continued)

TYPE		MODEL NUMBER	Static Pressure	Option		
MSP Duct (2nd Gen)	Large	4MUD4536A10N0*	0.7"	0100EC-1A5E12-276470-370005		
			0.8"	0100EC-1A5E34-276470-370005		
		4MUD4542A10N0*	0.2"	0100EC-1A194D-277D8C-370005		
			0.3"	0100EC-1A597E-277D8C-370005		
			0.4"	0100EC-1A5AA1-277D8C-370005		
			0.5"	0100EC-1A5AD3-277D8C-370005		
			0.6"	0100EC-1A5E06-277D8C-370005		
			0.7"	0100EC-1A5E38-277D8C-370005		
			0.8"	0100EC-1A5E5A-277D8C-370005		
			4MUD4548A10N0*	0.2"	0100EC-1A1A81-278CA0-370005	
		0.3"		0100EC-1A5AA2-278CA0-370005		
		0.4"		0100EC-1A5AD4-278CA0-370005		
		0.5"		0100EC-1A5E06-278CA0-370005		
		0.6"		0100EC-1A5E38-278CA0-370005		
		0.7"		0100EC-1A5E6A-278CA0-370005		
		0.8"		0100EC-1A5E7D-278CA0-370005		
		MSP Duct (3rd Gen)		Small	4MUD4518B10N0*	0.1
			0.24"			01B0EC-1E54AA-27343B-374000
			0.35"			01B0EC-1E5933-27343B-374000
			0.47"			01B0EC-1E59CC-27343B-374000
0.6"	01B0EC-1E5E44-27343B-374000					
Medium	4MUD4524B10N0*		0.1	01B0EC-1E5407-274750-374020		
			0.24"	01B0EC-1E547B-274750-374020		
			0.35"	01B0EC-1E55D1-274750-374020		
			0.47"	01B0EC-1E5937-274750-374020		
			0.6"	01B0EC-1E599D-274750-374020		
			0.7"	01B0EC-1E5AF3-274750-374020		
			0.8"	01B0EC-1E5E59-274750-374020		
	4MUD4530B10N0*		0.16"	01B0EC-1E54B8-275A64-376020		
			0.3"	01B0EC-1E5920-275A64-376020		
			0.47"	01B0EC-1E5997-275A64-376020		
Large	4MUD4536B10N0*		0.6"	01B0EC-1E5D0E-275A64-376020		
			0.7"	01B0EC-1E5E64-275A64-376020		
			0.8"	01B0EC-1E5ECA-275A64-376020		
			0.16"	01B0EC-1E5403-276470-376045		
			0.3"	01B0EC-1E546A-276470-376045		
			0.47"	01B0EC-1E55D1-276470-376045		
	4MUD4542B10N0*		0.6"	01B0EC-1E5926-276470-376045		
			0.7"	01B0EC-1E5959-276470-376045		
			0.8"	01B0EC-1E597B-276470-376045		
			0.16"	01B0EC-1E5424-277D8C-377045		
			0.3"	01B0EC-1E547B-277D8C-377045		
			0.47"	01B0EC-1E55E2-277D8C-377045		
			0.6"	01B0EC-1E5937-277D8C-377045		
			0.7"	01B0EC-1E596A-277D8C-377045		
			0.8"	01B0EC-1E598C-277D8C-377045		
4MUD4548B10N0*	0.16"	01B0EC-1E5468-278CA0-377045				

Mini-Split Product Option Codes (continued)				
TYPE		MODEL NUMBER	Static Pressure	Option
MSP Duct (3rd Gen)	Large	4MUD4548B10N0*	0.3"	01B0EC-1E54AC-278CA0-377045
			0.47"	01B0EC-1E5913-278CA0-377045
			0.6"	01B0EC-1E5948-278CA0-377045
			0.7"	01B0EC-1E597B-278CA0-377045
			0.8"	01B0EC-1E59AE-278CA0-377045

Questions

This document is intended to assist the design professional with understanding when it is possible to modify the product option code for Trane ProSpace™ VRF, and or Mini-Split systems. This document is not valid for any other purpose. These guidelines do not change or mitigate the liability of the installing contractor.

For further questions, if you are an authorized Trane Distributor or a Commercial Sales Office, contact VRF Product Support or VRF Technical Support. If you are not a Trane distributor or a Commercial Sales Office, please contact your local Trane distributor or Commercial Sales Office.

Ingersoll Rand has a policy of continuous product and product data improvements, and reserves the right to change design and specifications without notice.