

IP UNITS TOLERANCE: TRANE STD ES1102D02
UNLESS OTHERWISE SPECIFIED

.X = ±
.XX = ±
.XXX = ±

FINISH ✓

ANGLES = ± * HOLE DIA = ±

CONFORMS TO ASME Y14.5M-1994.

AUTOCAD

DO NOT SCALE
PRINT

DRAWN BY:
HK Pass
DATE: 10-23-01
SIMILAR TO:

THE TRANE COMPANY

A DIVISION OF
AMERICAN STANDARD INC.

THIS DRAWING IS PROPRIETARY AND
SHALL NOT BE COPIED OR ITS
CONTENTS DISCLOSED TO OUTSIDE
PARTIES WITHOUT THE WRITTEN
CONSENT OF THE TRANE COMPANY

THIRD ANGLE
PROJECTION

X19051328

REV
D

WIRE ASSY

| No. | PART NAME | MATERIAL | DRAWING, PART OR MATERIAL NO | PART QUANTITY |
|-----|--------------------------------------------------|----------|------------------------------|---------------|
| 1 | #6 INSULATED FORK CONNECTOR | | PNF18-6FN-3K | 3 |
| 2 | CONNECTOR, MTA-100 IDC POSTED, CLOSED END, 22AWG | | AMP 0-647000-6 | 1 |
| 3 | CONNECTOR, MTA-100 IDC, CLOSED END, 22AWG | | AMP 0-640440-6 | 1 |
| 4 | CABLE, 3 CONDUCTOR, 22 AWG, TYPE CL2P | | | 144.00" |
| 5 | PANDUIT STRAIN RELIEF | | PLWP1S-D30 | 2 |
| 6 | HEYCO STAR BUSHING #2119 | | X19100042-03 | 1 |
| 7 | 300V WIRE, 22 AWG, RED, UL1007/1569 | | TBD | 12.00" |
| 8 | 300V WIRE, WIRE, 22 AWG, WHITE, UL1007/1569 | | TBD | 18.00" |
| 9 | 300V WIRE, WIRE, 22 AWG, BLACK, UL1007/1569 | | TBD | 12.00" |
| 10 | POLYOLEFIN SHRINK TUBE, 3/16" X 1 1/4" | | TBD | 3 |
| 11 | AMTRONICS BUTT SPLICE | | 076D18B | 3 |

