

TOLERANCE  
UNLESS OTHERWISE SPECIFIED

.X = ±  
.XX = ±  
.XXX = ±

FINISH ✓

ANGLES = ± ° HOLE DIA = ±

CONFORMS TO ASME Y14.5M-1994.

AUTOCAD

DO NOT SCALE  
PRINT

DRAWN BY:  
A. CERNIGLIA

DATE: 8-11-97

SIMILAR TO:  
X13140738

THE TRANE COMPANY  
A DIVISION OF  
AMERICAN STANDARD INC.

THIS DRAWING IS PROPRIETARY AND  
SHALL NOT BE COPIED OR ITS  
CONTENTS DISCLOSED TO OUTSIDE  
PARTIES WITHOUT THE WRITTEN  
CONSENT OF THE TRANE COMPANY

THIRD ANGLE  
PROJECTION

X13140853

REV  
B

HEATER  
STRIP  
(HEAT TAPE)  
W/GROUND WIRE

EXT	A	WATTS	VOLTS	B	LEAD TERMINATION
01	30 FT	210	120	60 IN	1/4 FEMALE QC TERMINALS— STRAIGHT EACH LEAD (AMP #41274)
02	60 FT	420	120	60 IN	STRIP .500 ±.06
03	60 FT	420	240	60 IN	
04	80 FT	560	120	60 IN	
05	80 FT	560	240	60 IN	
06	60 FT	420	120	120 IN	1/4 FEMALE QC TERMINALS— STRAIGHT EACH LEAD (AMP #41274)
07	60 FT	420	240	120 IN	STRIP .500 ±.06
08	6 FT	42	120	60 IN	
09	12 FT	84	120	60 IN	

SPECIFICATIONS:

THERMOSTAT SET TO TURN TAPE ON AT APPROX 38°F ± 3°  
AND OFF AT APPROX 63°F ± 10°

TAPE TO BE RECOGNIZED FOR OUTDOOR USE

