


<p style="text-align: center;">TOLERANCE UNLESS OTHERWISE SPECIFIED</p> <p>.X = ± .XX = ± .XXX = ±</p> <p style="text-align: right;">FINISH ✓</p> <p>ANGLES = ± ° HOLE DIA = <math>\frac{+}{-}</math></p> <p style="text-align: center;">CONFORMS TO ASME Y14.5M-1994.</p>	AUTOCAD	<b>THE TRANE COMPANY</b> A DIVISION OF AMERICAN STANDARD INC.	X13140891	REV F	
	DO NOT SCALE PRINT		THIS DRAWING IS PROPRIETARY AND SHALL NOT BE COPIED OR ITS CONTENTS DISCLOSED TO OUTSIDE PARTIES WITHOUT THE WRITTEN CONSENT OF THE TRANE COMPANY	HEATER SUBMERSIBLE	
	DRAWN BY: J. HARSTAD DATE: 8-30-00				
	SIMILAR TO:	 THIRD ANGLE PROJECTION			

SPECIFICATIONS:

NOTES:

VOLTS - 120

VENDOR P/N, VOLTS & WATTS TO BE STAMPED ON HEATER

1. MUST BE UL LISTED OR RECOGNIZED & CSA CERTIFIED. C-UR (UL RECOGNIZED PER CANADIAN STANDARDS) IS ACCEPTABLE IN LIEU OF BEING CSA CERTIFIED
2. OPERATING PRESSURE RANGE - 350 PSIG
3. 18 GA LEAD WIRES
4. INSULATION 300V 250C
5. HEATER TO BE SUITABLE FOR USE IN MOIST LOCATIONS

EXT	WATTS	A	B	C
-01	400	6.94	5.46	96.0
-02	600	7.50	6.02	120.0
03	400	6.94	5.46	96.0
04	600	7.50	6.02	120.0
05	400	4.48	3.00	144.0
06	600	6.50	5.02	144.0

