

NOTES:
1. SWITCH ACTION: SPST. NORMALLY CLOSE
OPENS ON TEMPERATURE DECREASE
2. CAPILLARY FORMED Ø 2.50 AROUND
CONTROL FOR SHIPMENT.

CONTROL RATING GE			CONTROL RATING SELCO		
VOLTS AC	120V	240V	VOLTS AC	125V	250V
AMPS FL	10.0	5.0	AMPS FL	1-20	1-20
AMPS LR	60.0	30.0	AMPS LR	1-80	1-80

UNLESS OTHERWISE SPECIFIED ALL
DIMENSIONS ARE IN INCHES.
TOLERANCE:
.X = ±
.XX = ±
.XXX = ±
ANGLES = ± °
HOLE DIA = ±
CONFORMS TO ASME Y14.5M-1994.

TRANE
THIS DRAWING IS PROPRIETARY AND SHALL NOT BE COPIED OR ITS
CONTENTS DISCLOSED TO OUTSIDE PARTIES WITHOUT THE WRITTEN
CONSENT OF TRANE
DRAWN BY: KASPER
TRANE DATE: 07/16/92
THIRD ANGLE PROJECTION
DO NOT SCALE PRINT

X13100276
CONTROL
DEFROST/FREEZE
SHEET 1 OF 1
REV L

EXT	DIM A +3.00 - 0.00	CALIBRATION ° F @ 29.35 HG					
		CLOSE ° F	OPEN ° F	REFRIG	CONTROL TYPE	MFG NAME	FIG
01	30.00	62±3°	39±2°	40	DEFROST	GE	1
02	24.00	44±3.6°	36±2.7°	—	FREEZE	GE	1
						SELCO	2
03	90.00	44±3.6°	36±2.7°	—	FREEZE	GE	1
						SELCO	2
04	50.00	44±3.6°	36±2.7°	—	FREEZE	GE	1
						SELCO	2
05	80.00	44±3.6°	36±2.7°	—	FREEZE	GE	1
						SELCO	2
06	100.00	44±3.6°	36±2.7°	—	FREEZE	GE	1
						SELCO	2
07							
08	30.00	45±3°	24±2°	—	DEFROST	GE	1
						SELCO	2
09	30.00	55±3.6°	39±2.7°	40	DEFROST	GE	1
						SELCO	2

FIG 1

FIG 2

