



TWA2404*D

Refrigerant charging curves:



TWA superheat with matched TWE air handler:

Condenser	Air Handler	Cooling Superheat (°F)		Heating Superheat (°F)	
		Circuit 1	Circuit 2	Circuit 1	Circuit 2
TWA2404*D	TWE2404*B	10.5	18.8	8.5	7.7

Refrigerant charge table and line size with matched TWE air handler:


Matched Set	Refrigerant Charge (lbs)		Per Circuit	
	Circuit 1	Circuit 2	Liquid Line Diameter	Vapor Line Diameter
TWA2404*D w/ TWE2404*B	23.5	23.5	0.625 (5/8")	1.375 (1-3/8")

NOTE 1: Charge amount listed is for 25 ft line length.


NOTE 2: Base matched unit charge is 20.4 lbs for each circuit. Additional charge is 1.96 ounces of refrigerant per foot of line set as specified in table above. For additional information refer Application guide SS-APG008*-EN

Pressure curve TWA2404*D with TWE2404*B (Cooling)

Circuit 1




Circuit 2



Pressure curve TWA2404*D with TWE2404*B (Heating)

Circuit 1



Circuit 2

