


# TTA3004\*C

## Refrigerant charging curve:



## Pressure curve TTA3004\*C with TWE3004\*B:

## TTA superheat with matched TWE air handler:

Condenser	Air Handler	Cooling Superheat (°F)	
		Circuit 1	Circuit 2
TTA3004*C	TWE3004*B	11.8	-


## Refrigerant charge table and line size with matched TWE air handler:

Matched Set	Refrigerant Charge (lbs)		Per Circuit	
	Circuit 1	Circuit 2	Liquid Line Diameter	Vapor Line Diameter
TTA3004*C w/ TWE3004*B	29.8	N/A	0.625 (5/8")	2.125 (2-1/8")

NOTE 1: Charge amount listed is for 25 ft line length.

NOTE 2: Base matched unit charge is 26.0 lbs. Additional charge is 2.41 ounces of refrigerant per foot of line set as specified in table above. For additional information refer Application guide SS-APG008\*-EN

Suction Pressure at 350 CFM/Ton



Discharge Pressure at 350 CFM/Ton

